



Rotary Evaporator

Rotary Evaporator



Rotary Evaporator

Rotary evaporators (also known as “Rotovaps”) are mainly used for distillations/separation applications often used for medicinal chemistry, pharmaceutical, chromatography, and petrochemical fields. In summary the system works by increasing the rate of evaporation of the solvent by

- (1) reducing the pressure to lower the solvent boiling point
- (2) rotating the sample to increase the effective surface area
- (3) heating the solution
- (4) then the evaporated solvent then condenses in a cooled glass condenser.

BEING Rotary Evaporator features

- Simple design for one handed operation manually or automatically.
- A unique PTFE sealing system provides exceptional thermostability, minimizes corrosion, and helps to ensure day in day out headache free operation.
- Our Bath offers a dual heating mode for water and oil with overheat protection.
- PID controller offers easy input of parameters and large LCD display for easy viewing.
- Vacuum regulator available.

Double temperature protection



PTFE dual seal



Clamp




M14 threaded fittings for chiller



Independent temperature limit controller

High efficiency can be cycle used for two Rotary Evaporators



Standard :DIN-12880

Independent temperature safety equipment, 2 class (DIN12880) .

Cooling





Reduce pressure



Working condition


- Ambient temp 20°C , AC 220V-240V, 60Hz
- 1L Rotary bottle, Water 500ml
- Water Bath temp: Set at 40°C
- Coolant (alcohol/water): set the temperature at 10°C
- Rotation speed: 120rmp




Technical parameters

	Model	GentianaRV-21M	GentianaRV-21A
Performance	Rotation speed	20-180rpm	
	Water bath temperature range	Water: RT+5~99°C , Oil: RT+5~180°C (Option)	
	Evaporating speed	22ml/min	
	Ultimate vacuum	8mbar	
Features	Speed setting	LCD display with knob	
	Lifting mode	Manual	automatic
	Motor function	N/A	DC brushless motor
Structure and composition	Main motor DC brushless	DC brushless motor	
	Condenser	Snake Condensate Condensate Area 0.15m ² , 1L Rotary Bottle, 1L Collecting Bottle, TS29 / 38 Bottle Clamp, Ball Face S35 / 20	
	Vacuum seal	PTFE and Teflon Coating	
Heating bath	Interior water bath size	Φ 230mmx130mm	
	Water bath material	Stainless steel Corrosion resistant coating	
	Heating power	1000W	
Temperature range		5~35°C	
Electrical input		AC 220V-240V, 60Hz	


Rotary Evaporator



Features




- Scheduled operation
- Rpm set/ display
- Temperature set/ display
- Running status



One-button operation


- Ⓐ Long press to lift or lower the bath
- Ⓑ Press to heat the bath
- Ⓒ Press to start/ stop rotating



■ Evaporating ability


Ambient temperature: 20°C

▲t means: the difference between steam and water bath



■ Vacuum degree


Vacuum pump required
Flow rate: 50L/min



■ Water bath heating

Ambient temp.: 20°C
Medium: Water

Power: AC 220V-240V, 60Hz
Set: 80°C



Technical parameters

Model	GentianaRV-5A	GentianaRV-10A	GentianaRV-20A	GentianaRV-50A	
Size	5L	10L	20L	50L	
Performance	Rotation speed (rpm)	20-140	20-130	20-130	
	Evaporate rate (Max. L/h))	2	3.5	4	
	Ultimate degree(mbar)	8mbar			
	Temperature rate(°C)	Water: RT+5~99°C , Oil: RT+5~180°C (Option)			
	Temperature stability (°C)	±1			
Function	Controller	PID controller			
	Safety	1.Over current protection 2. Over temp. protection 3. Power interruption alarm 4. Anti-dry protection			
	Display	LCD screen			
	Lift mode	Auto lift			
	Power (W)	2300	3300	4300	5300
	Condensation area(M ²)	0.28	0.49	1.29	1.75
	Capability of rotatory bottle	5L	10L	20L	50L
	Capability of collecting bottle	3L	5L	10L	20L
	Sealing gasket	PTFE and Teflon Coating			
Water Bath	Lifting distance(mm)	150	170	170	260
	Bracket	No	Aluminum alloy bracket		
	Dimension(mm)	Diameter 280×175	Diameter 365×225	Diameter 445×250	Diameter 552×320
Interface size	Material	SUS304 Water Bath + PTFE Teflon coating			
	Condenser barb size(mm)	14	18		
Exterior dimension (including glasswares) W×D×H(mm)		860×410×1120	1100×540×2060	1200×570×2060	1300×610×2150
Power		AC 220V-240V, 60Hz			
Ambient temperature		10-35°C			